

## Bench Top Ring Mill

BTRM | Quiet and efficient pulveriser.



### The main features.

- Small and compact to fit on a work bench.
- Very low contamination of samples
- Low maintenance
- Noise level less than 80 dBA

### The process.

Used for pulverising a variety of material from 1g - 100g for subsequent analysis by instrumental methods or wet chemistry.

## Bench Top Ring Mill

BTRM | Quiet and efficient pulveriser.

### Specifications

|                             |   |
|-----------------------------|---|
| Motor power                 | 0.18kW, 3 phase or single phase   |
| Maximum input particle size | Recommended 2-5mm sample, 8mm maximum.  |
| Product size                | Typically 95% - 100µm, samples can be pulverized <75µm  |
| Width x Height x Depth      | 410 x 510 x 410mm   |
| Weight                      | 67kg  |
| Sample size                 | 1g - 100g   |
| Dust extraction             | NA  |
| Options                     | NA  |
| Warranty                    | Rocklabs Bench Top Ring Mill is sold with a 2000 operating hours or one year warranty (whichever comes first), covering all parts (excluding wear parts) and labour if used under normal laboratory conditions. |

### \*Head Options

|                  |     |
|------------------|-----|
| Carbon / Chrome  | 40  |
| Carbon / Chrome  | 100 |
| Tungsten Carbide | 40  |
| Zirconia         | 40  |

### Shipping Dimensions

|        |       |
|--------|-------|
| Width  | 665mm |
| Height | 685mm |
| Depth  | 610mm |
| Weight | 80kg  |

\*For more information please contact us on the details below or visit the website for a list of international agents.

**ROCKLABS Ltd.**  
P.O Box 18-142, Glen Innes 1743,  
Auckland, New Zealand.

**P** 64 9 634 7696  
**F** 64 9 634 6896  
**E** [sales@rocklabs.com](mailto:sales@rocklabs.com)

[www.rocklabs.com](http://www.rocklabs.com)